



FUZZYSCAN A780 HC

Antimicrobial 2D Handheld Imager



Powerful 2D scanner designed for hygiene-conscious applications

Cross-contamination is a risk in hospitals, clinics, laboratories, food processing plants and similar establishments. With its robust enclosure and antimicrobial properties, Cino's A780 HC is ideal for the tough demands of hygiene-conscious industries. When circumstances require silent signaling, the built-in vibrator can provide tactile confirmation of successful reads. A780 HC's superior performance helps you get the job done with maximum efficiency.

- Disinfectant-ready enclosure with antimicrobial additives
- Compliance with JIS Z2801:2000 antimicrobial standard
- Reads various challenging and problematic barcodes
- Superior first-time read
- Rapid omni-directional scanning
- Reads electronic barcodes from smartphone screens
- Withstands drops from 2.0m to concrete
- Standard-Range and High-Density models
- Clear audio and visual feedback
- Built-in vibrator for tactile confirmations
- Configuration can be done through iCode
- Advanced data formatting with DataWizard Premium
- System security development using DataWizard Premium

Sanitation-Friendly

Disinfectant-Ready Enclosure

The scanner's housing is disinfectant-ready, and can be wiped down with Cino's recommended cleaning solutions (see Specifications below). It is specially designed for the needs of hygiene-conscious establishments.

Inclusion of Antimicrobial Additives

The housing's plastic material also incorporates a silver inorganic antimicrobial agent that will not wear off during its lifetime. This provides an extra layer of protection against the growth of microorganisms.

Compliance with Antimicrobial Standard

This scanner complies with the JIS Z2801:2000 antimicrobial standard. It is ideal for industries where the cleanliness of work tools is prioritized, such as healthcare or food processing.

Scan All Your Needs

Exceptional Imaging Platform

Cino's FuzzyScan imaging platform combines the latest advancements in image processing, electro-optics, computing architecture, and barcode decoding. It also makes use of Machine Learning Algorithm to enhance dynamic exposure control, pattern finding, image processing, as well as historical control.

This exceptional platform is built into Cino scanners, maximizing the speed and quality of data captures.



Hospital



Laboratory



Pharmacy

Ready for Challenges

Empowered by the FuzzyScan imaging platform, this scanner is designed to capture a vast array of challenging and problematic barcodes. For example: distorted, dirty or damaged barcode labels, or electronic barcodes on dimly-lit displays.

Complete Lineup to Fulfill Diverse Requirements

Scanning applications are increasingly diverse, and specialized tools may be needed to get the job done. For this reason, Cino has made this scanner available in different models: Standard-Range and High-Density.

The Standard-Range model is designed to fulfill most scanning requirements. Enabled by advanced technologies, this model offers superior reading performance on both regular and high-density barcodes. It is suitable for a wide range of applications that would normally require different types of scanners.

The High-Density model, on the other hand, is built to read very small, high-density 2D barcodes that appear on items such as electronic components, jewelry tags, or medical equipment. Users can choose the model that best suits their needs.

Enhanced User Experience

Simple and Intuitive Scanning

With omni-directional reading capabilities, this scanner's operation is straightforward and user-friendly. There is no need to pre-align with the barcode, which makes your scanning experience intuitive, fast and effortless.

Sharp Aimer for Rapid Targeting

The scanner's "round spot" LED beam helps users aim faster and with greater accuracy. A separate background light is also projected to further expedite barcode capture; this bright red illumination is particularly useful under low ambient lighting.

Clear Audio, Visual and Tactile Feedback

This barcode scanner contains a programmable beeper with adjustable sound volume. Its LED lights provide conspicuous, multi-color indications.

A built-in vibrator offers tactile confirmation of good reads. It is ideal for instances where the scanner's beeping sounds might disturb patients, or when they are difficult to hear because of loud background noise.

Built for Lasting Performance

This scanner merges durability and ergonomics without compromising style. Thanks to an over-mold construction, this robust device can withstand 2.0-meter drops to concrete. The handle is ergonomically designed and offers a natural, comfortable grip. Furthermore, its sleek appearance is sure to complement any professional decor.

Value Beyond Measure

Simplified Configuration Process

The iCode is a configuration barcode designed to simplify and accelerate your scanner set-up process. It can be embedded with more than one command, thereby enabling the simultaneous change of numerous parameters. Instead of configuring their Cino scanners with multiple barcodes, users can achieve the same results with a single iCode.

Simply choose your desired settings in the FuzzyScan PowerTool, and click on the "iCode" button to generate a comprehensive barcode that embodies them all.

Customized Functionalities

DataWizard Premium lets you write data or security scripts which can then be used to program Cino scanners for customized tasks. The script language is similar to BASIC and easy to learn for experienced programmers.

This exceptional feature is included in the FuzzyScan PowerTool and offered to Cino clients without extra charge.

Advanced Data Formatting

Data scripts can be used to configure your scanners for intricate formatting procedures that would otherwise be assigned to the host device. For example: parsing raw data captured from a driver's license, adding prefixes or suffixes, and more.

System Security

Cino devices can be programmed via security scripts to participate in system protection. Set your host system to prompt scanners for an algorithm-generated key, and to refuse connection if such key is not provided. Develop a security script containing the said algorithm so that it may deliver the correct key. Install the security script on approved scanners only. This set-up will help prevent unauthorized scanners from connecting with the host system.

SPECIFICATIONS

Performance Characteristics

Image Sensor	1280 x 800 Pixels
Print Contrast	18% minimum reflectance difference
Light Source	660nm LED
Imager Field of View	41.5° H x 25.9° V
Minimum Resolution	HD Model 2.4 mil Code 39, 4.5 mil DM SR Model 2.7 mil Code 39, 4.8 mil DM
Reading Range *1	HD Model 13 mil (0.33mm) UPC/EAN up to 14.1" SR Model 13 mil (0.33mm) UPC/EAN up to 19.6"
Roll, Pitch, Skew	Roll: 360° ; Pitch: ± 75° ; Skew: ± 65°
Motion Tolerance	Up to 617 cm/s (243 in/s)
Configuration Setup	FuzzyScan Barcode commands FuzzyScan iCode FuzzyScan PowerTool
Data Processing	DataWizard Premium
Host Interfaces	USB HID (USB Keyboard) USB VCOM (USB COM port emulation) Standard RS232
Image Capture	BMP

Physical Characteristics

Dimensions	93.5 mm (L) x 71 mm (W) x 160 mm (D) 3.68 in. (L) x 2.79 in. (W) x 6.29 in. (D)
Weight	150g (cable excluded)
Color	Healthcare White
User Interfaces	3 LEDs for power, good read and status indications Programmable beeper Vibrator
Operating Voltage	5VDC ± 10%
Operating Current	Operating : Typical 395 mA @5VDC Standby : Typical 220 mA @5VDC
Antimicrobial Additives	Silver inorganic antimicrobial agent

1. The Reading Range are measured under Cino's test environmental condition.
2. Don't stare into the LED beam.

Supported Symbolologies

1D Linear Codes	Code 39, Code 39 Full ASCII, Code 32, Code 128, GS1-128, Codabar, Code 11, Code 93, GS1 DataBar, Standard & Industrial 2 of 5, Interleaved & Matrix 2 of 5, IATA, UPC/EAN/JAN, UPC/EAN/JAN with Addendum, Telepen, MSI/Plessey & UK/Plessey
2D Codes	PDF417, Micro PDF417, Codablock F, Code 16K, Code 49, Composite Codes, DataMatrix, MaxiCode, QR Code, Aztec, MicroQR
Postal barcodes	Australian Post, US Planet, US Postnet, Japan Post Posi LAPA 4 State Code

User Environment

Drop Specifications	Withstands multiple drops from 2m (6.6ft) to concrete
Environmental Sealing	IP42
Operating Temperature	-10 °C to 50 °C (14 °F to 122 °F)
Storage Temperature	-40 °C to 70 °C (-40 °F to 158 °F)
Humidity	5% to 95% relative humidity, non-condensing
Ambient Light Immunity	0 ~ 106,000 lux
ESD Protection	Functional after 15KV discharge
Recommended cleaning solutions	Gentle dish soap water or alcohol solvent solutions

Safety & Regulatory

EMC	CE, FCC, BSMI, C-Tick, KC, VCCI
Safety *2	LED Eye Safety IEC62471, Exempt Group
Environmental	Compliant with RoHS directive
Antimicrobial	JIS Z2801 : 2000

Accessories

Cables	RS232 Serial Cable USB Cable USB Power Supply Cable
Others	5VDC Power Supply Unit US100 Smartstand US50 Hands-Free Stand

